

characteristics Isitec 2 with castors

Article: 9608 integral foam

Dimensions in mm	Backrest:	H:	340
	Seat:	H:	430-600
		B:	440
		T:	410
Packing data	Weight	kg	12,0
	Volume	m ³	0,13



Base equipment

Benefit

Backrest	<p>Ergonomically designed, high backrest to take the strain off the spine and muscles This is achieved by means of its special shape: wide at the bottom and narrow at the top</p> <p>Backrest height adjustment convenient and easy to handle in sitting position</p> <p>Carrying handle integrated</p>	<p>The backrest optimum support for your lumbar region whilst allowing your arms and upper body the space and freedom they need higher up in order to move around</p> <p>The amount of the support can be provided in accordance with the user's body size</p> <p>Suitable to handle the chair more easily</p>
Seat	<p>Ergonomically designed, extra high seat. With rounded front edge</p>	<p>The round front edge of the seat prevents blocked circulation in the thighs</p>
Seat and backrest design	<p>Integral foam (PU): The new developed SoftTouch integral foam provides the ultimate softness in seating, is washable and resistant to external influences Colour: Black (2000)</p>	<p>The use of integral foam is recommended for work environments where the chair is in contact with aggressive substances and sharp parts</p>
Seat height	<p>Stepless seat height setting from 430-600 mm supported by safety gas spring with protective cover</p>	<p>Seat height can be adapted to nearly 95% of all body sizes, the cover protects the gas spring from dust and dirt</p>
Technology	<p>Permanent contact backrest with additional seat inclination adjustment</p> <p>Quick adjustment</p>	<p>This mechanism ensures that the backrest responds immediately to any movements of the upper body by following them. Thus, the back remains supported all the time. The backrest can also be locked into any tilt position if required</p> <p>There is a continuously variable mechanism for tilting the seat forwards. This ensures that your posture remains relaxed even when you need to bend forwards into your work. Less pressure is exerted on the thigh area, which encourages steady circulation. The problem of sitting all hunched up is masterfully avoided thanks to a mechanism that ensures a minimum angle of 90° between your legs and upper body at all times</p> <p>Every function can be operated comfortable and easy in sitting position</p>
Base	<p>Black 5 star base made from plastic. Flat design</p>	<p>Very high stability, longevity and safety Flat design prevents stumbling hazard</p>
Castors	<p>Dual-wheel safety castors with load-sensitive brakes, For hard floors as standard</p>	<p>Chairs are braked when not used which decreases the accident risk</p>
Materials	<p>All materials are separable and recyclable.</p>	<p>Environmentally friendly.</p>

characteristics Isitec 2 with castors

Article: 9608 integral foam

Dimensions in mm	Backrest:	H:	340
	Seat:	H:	430-600
		B:	440
		T:	410
Packing data	Weight	kg	12,0
	Volume	m ³	0,13



Standards	DIN 68 877
	German GS "safety tested" mark of conformity
	Quality management system DIN EN ISO 9001
	EEC Directive No. 1836/93 and
	Environmental management system DIN EN ISO 14001

Procuring is insured

Warranty	10 year long term warranty, 3 years full warranty
----------	---

Guaranteed quality and high efficiency

characteristics Isitec 2 with castors

Article: 9608 integral foam

Dimensions in mm	Backrest:	H:	340
	Seat:	H:	430-600
		B:	440
		T:	410
Packing data	Weight	kg	12,0
	Volume	m ³	0,13



Options	Benefit		
<table border="0"> <tr> <td style="vertical-align: top;">Armrests</td> <td> <ul style="list-style-type: none"> Loop armrest Multifunctional armrest </td> </tr> </table>	Armrests	<ul style="list-style-type: none"> Loop armrest Multifunctional armrest 	<p>Made of polyamide, adjustable in width (20 mm)</p> <p>The armrests are adjustable in height, width and depth to suit the individual user</p>
Armrests	<ul style="list-style-type: none"> Loop armrest Multifunctional armrest 		
<table border="0"> <tr> <td style="vertical-align: top;">Accessories</td> <td> <ul style="list-style-type: none"> Foot ring </td> </tr> </table>	Accessories	<ul style="list-style-type: none"> Foot ring 	<p>The foot ring can be retrofitted by attaching it to the chair column</p>
Accessories	<ul style="list-style-type: none"> Foot ring 		
<table border="0"> <tr> <td style="vertical-align: top;">Options</td> <td> <ul style="list-style-type: none"> Steel base </td> </tr> </table>	Options	<ul style="list-style-type: none"> Steel base 	
Options	<ul style="list-style-type: none"> Steel base 		